

Cable glands Progress® nickel-plated brass for high temperature application



Long entry thread metric

Type approval: Progress MS HT

- One-piece sealing insert
- not overall length insulated

Order number:	1100.25.91.205
E-No:	121282608
EAN:	7611614132105
Material	Nickel-plated brass
Seal	FPM
O-ring	FPM
Operation temperature	-40°C / +200°C
Strain relief	Version A acc. to EN 62444
Protection class	IP 68 (up to 10 bar) / IP 69
Entry thread	M25x1.5
Clamping range min.	16.0 mm
Clamping range max.	20.5 mm
Wrench size	30 mm
Dimension H	28 mm
Thread length L	11 mm
Dispatch	25

1 = Metric coarse-pitch thread (with VDE test report)