

Cable glands Progress® stainless steel A2 for high temperature applications



Long entry thread metric

Type approval: Progress S2 HT

- One-piece sealing insert
- not overall length insulated

Order number:	1100.32.96.255
E-No:	121613708
EAN:	7611614133768
Material	CrNi stainless steel A2 (DIN EN 1.4305 / AISI 303)
Identification	1 groove
Seal	FPM
O-ring	FPM
Operation temperature	-40°C / +200°C
Strain relief	Version A acc. to EN 62444
Protection class	IP 68 (up to 10 bar) / IP 69
Entry thread	M32x1.5
Clamping range without insert min.	21.0 mm
Clamping range without insert max.	25.5 mm
Wrench size	36 mm
Dimension H	28 mm
Thread length L	13 mm
Dispatch	25

1 = Metric coarse-pitch thread (with VDE test report)