

## Cable glands Syntec® nickel-plated brass with lamellar technology



### Long entry thread metric

#### Type approval: SYNTEC MS

- One-piece sealing ring
- not overall length insulated

<b>Order number:</b>	<b>1145.20.130</b>
E-No:	121342618
EAN:	7611614230153
Material	Nickel-plated brass
Sealing ring	TPE
O-ring	NBR
Lamellar insert	Polyamide PA 6
Operation temperature	-40°C / +100°C
Strain relief	Version A acc. to EN 62444
Protection class	IP 68
NEMA Type rating	4X
Entry thread	M20x1.5
Clamping range min.	7.0 mm
Clamping range max.	13.0 mm
Wrench size	22 mm
Dimension H	25 mm
Thread length L	12 mm
UL - clamping range	9.7-13.0 mm
Dispatch	50