

Cable glands Syntec® nickel-plated brass with lamellar technology



Long entry thread metric

Type approval: SYNTEC MS

- One-piece sealing ring
- not overall length insulated

Order number:	1145.25.110
E-No:	121342708
EAN:	7611614230184
Material	Nickel-plated brass
Sealing ring	TPE
O-ring	NBR
Lamellar insert	Polyamide PA 6
Operation temperature	-40°C / +100°C
Strain relief	Version A acc. to EN 62444
Protection class	IP 68
NEMA Type rating	4X
Entry thread	M25x1.5
Clamping range min.	5.0 mm
Clamping range max.	11.0 mm
Wrench size	28 mm
Dimension H	31 mm
Thread length L	12 mm
UL - clamping range	8.0-11.0 mm
Dispatch	25