

## Cable glands Progress® EMC nickel-plated brass with contact sleeve for high

**Long entry thread metric**

- One-piece sealing insert
- not overall length insulated

<b>Order number:</b>	<b>1180.17.91.080</b>
EAN:	7611614233505
Material	Nickel-plated brass
Contact sleeve	Nickel-plated brass
Seal	FPM
O-ring	FPM
Operation temperature	-40°C / +200°C
Strain relief	Version A acc. to EN 62444
Protection class	IP 68 (up to 10 bar) / IP 69
Properties	Excellent shield contact through the contact sleeve with the braided shield terminating in the screwed cable gland
Entry thread	M16x1.5
Clamping range without insert min.	6.0 mm
Clamping range without insert max.	8.0 mm
Wrench size	18 mm
Dimension H	23 mm
Thread length L	10 mm
Dispatch	50

1 = Metric coarse-pitch thread