

## Cable glands Progress® EMC nickel-plated brass with contact sleeve



### Long entry thread Pg

#### Type approval: Progress MS EMV

- One-piece sealing insert
- not overall length insulated

<b>Order number:</b>	<b>1180.21.160</b>
E-No:	121038508
EAN:	7611614115290
Material	Nickel-plated brass
Contact sleeve	Nickel-plated brass
Seal	TPE
O-ring	NBR
Operation temperature	-40°C / +100°C
Protection class	IP 68 (up to 10 bar) / IP 69
NEMA Type rating	4X
Properties	Excellent shield contact through the contact sleeve with the braided shield terminating in the screwed cable gland
Entry thread	Pg 21
Clamping range without insert min.	13.0 mm
Clamping range without insert max.	16.0 mm
Wrench size	30 mm
Dimension H	30 mm
Thread length L	12 mm
Dispatch	25

Available with sealing inserts conformity with EN 45545 / NFPA 130. When placing an inquiry, prefix the article number by the capital F.