

## Cable glands Progress® nickel-plated brass for installation of multiple cables

**Short entry thread Pg**

- One-piece sealing insert
- not overall length insulated

|                                    |                      |
|------------------------------------|----------------------|
| <b>Order number:</b>               | <b>1310.11.2.075</b> |
| EAN:                               | 7611614138763        |
| Material                           | Nickel-plated brass  |
| Seal                               | TPE                  |
| O-ring                             | NBR                  |
| Operation temperature              | -40°C / +100°C       |
| Protection class                   | IP 68                |
| Entry thread                       | Pg 11                |
| Clamping range without insert min. | 5.5 mm               |
| Clamping range without insert max. | 7.5 mm               |
| Number of cables                   | 2                    |
| Wrench size                        | 24 mm                |
| Dimension H                        | 23 mm                |
| Thread length L                    | 6.0 mm               |
| Dispatch                           | 50                   |

Further versions and entry threads are available upon request.  
Available with sealing inserts conformity with EN 45545 / NFPA 130. When placing an inquiry, prefix the article number by the capital F.