

## Cable glands Progress® nickel-plated brass for installation of multiple cables

**Short entry thread metric****Type approval: Progress MS Multi**

- One-piece sealing insert
- not overall length insulated

<b>Order number:</b>	<b>1310.25.4.070</b>
E-No:	121161658
EAN:	7611614139661
Material	Nickel-plated brass
Seal	TPE
O-ring	NBR
Operation temperature	-40°C / +100°C
Strain relief	Version A acc. to EN 62444
Protection class	IP 68
Entry thread	M25x1.5
Clamping range without insert min.	5.5 mm
Clamping range without insert max.	7.0 mm
Number of cables	4
Wrench size	30 mm
Dimension H	28 mm
Thread length L	7 mm
Dispatch	25

Further versions and entry threads are available upon request.

Available with sealing inserts conformity with EN 45545 / NFPA 130. When placing an inquiry, prefix the article number by the capital F.