

Cable glands Progress® nickel-plated brass for installation of multiple cables

**Long entry thread metric****Type approval: Progress MS Multi**

- One-piece sealing insert
- not overall length insulated

Order number:	1311.20.3.050
E-No:	121171538
EAN:	7611614139937
Material	Nickel-plated brass
Seal	TPE
O-ring	NBR
Operation temperature	-40°C / +100°C
Strain relief	Version A acc. to EN 62444
Protection class	IP 68
Entry thread	M20x1.5
Clamping range without insert min.	3.5 mm
Clamping range without insert max.	5.0 mm
Number of cables	3
Wrench size	24 mm
Dimension H	23 mm
Thread length L	10 mm
Dispatch	50



Further versions and entry threads are available upon request.

Available with sealing inserts conformity with EN 45545 / NFPA 130. When placing an inquiry, prefix the article number by the capital F.