

Cable glands Progress® nickel-plated brass for installation of multiple cables

**Long entry thread metric****Type approval: Progress MS Multi**

- One-piece sealing insert
- not overall length insulated

| | |
|------------------------------------|----------------------------|
| Order number: | 1311.32.3.105 |
| E-No: | 121171728 |
| EAN: | 7611614140070 |
| Material | Nickel-plated brass |
| Seal | TPE |
| O-ring | NBR |
| Operation temperature | -40°C / +100°C |
| Strain relief | Version A acc. to EN 62444 |
| Protection class | IP 68 |
| Entry thread | M32x1.5 |
| Clamping range without insert min. | 8.5 mm |
| Clamping range without insert max. | 10.5 mm |
| Number of cables | 3 |
| Wrench size | 36 mm |
| Dimension H | 28 mm |
| Thread length L | 13 mm |
| Dispatch | 25 |



Further versions and entry threads are available upon request.

Available with sealing inserts conformity with EN 45545 / NFPA 130. When placing an inquiry, prefix the article number by the capital F.