

Synthetic cable glands Progress® GFK



Entry thread Pg

- Black RAL 9005
- One-piece sealing insert

Order number:	1540.09.105
EAN:	7611614139050
Material	Polyamide glass fiber reinforced
Properties	halogen-free
Seal	TPE
Operation temperature	-20°C / +100°C
Protection class	IP 68
Entry thread	Pg 9
Clamping range without insert min.	8.0 mm
Clamping range without insert max.	10.5 mm
Wrench size	21 mm
Dimension H	26 mm
Thread length L	12 mm
Dispatch	50