

## Synthetic cable glands Syntec® with lamellar technology



### Short entry thread metric

#### Type approval: SYNTEC

- Black RAL 9005
- One-piece sealing ring

<b>Order number:</b>	<b>1545.12.06</b>
E-No:	121756429
EAN:	7611614078243
Material	Polyamide PA 6
Properties	halogen-free, black UV resistant (tested according to EN ISO 4892-2)
Sealing ring	TPE or CR (Neoprene)
Operation temperature	-30°C / +100°C
Strain relief	Version A acc. to EN 62444
Protection class	IP 68
NEMA Type rating	4X
Entry thread	M12x1.5
Clamping range min.	2.5 mm
Clamping range max.	6.5 mm
Wrench size	15 mm
Dimension H	21 mm
Thread length L	6 mm
UL - clamping range	5.0-6.5 mm
Dispatch	100