

## Synthetic cable glands Syntec® with lamellar technology



### Entry thread Pg

#### Type approval: SYNTEC

- Black RAL 9005
- One-piece sealing ring

<b>Order number:</b>	<b>1545.42.38</b>
E-No:	121755929
EAN:	7611614078229
Material	Polyamide PA 6
Properties	halogen-free, black UV resistant (tested according to EN ISO 4892-2)
Sealing ring	CR (neoprene)
Operation temperature	-30°C / +100°C
Protection class	IP 68
NEMA Type rating	4X
Entry thread	Pg 42
Clamping range min.	28.0 mm
Clamping range max.	38.0 mm
Wrench size	60 mm
Dimension H	48 mm
Thread length L	15 mm
UL - clamping range	28.0-28.0 mm
Dispatch	5