

Synthetic cable glands Syntec® with lamellar technology



Short entry thread metric

Type approval: SYNTEC

- Light grey RAL 7035
- One-piece sealing ring

Order number:	1555.32.25
E-No:	121756819
EAN:	7611614078021
Material	Polyamide PA 6
Properties	halogen-free, black UV resistant (tested according to EN ISO 4892-2)
Sealing ring	TPE or CR (Neoprene)
Operation temperature	-30°C / +100°C
Strain relief	Version A acc. to EN 62444
Protection class	IP 68
NEMA Type rating	4X
Entry thread	M32x1.5
Clamping range min.	17.0 mm
Clamping range max.	25.0 mm
Wrench size	42 mm
Dimension H	36 mm
Thread length L	10 mm
UL - clamping range	19.5-23.0 mm
Dispatch	20

Available on request:

- Dark grey RAL 7001