

Synthetic cable glands Progress® GFK for installation of multiple cables



Entry thread Pg

- Light grey RAL 7035
- One-piece sealing insert

| | |
|------------------------------------|----------------------------------|
| Order number: | 1571.21.3.090 |
| EAN: | 7611614147857 |
| Material | Polyamide glass fiber reinforced |
| Properties | halogen-free |
| Seal | TPE |
| Operation temperature | -20°C / +100°C |
| Protection class | IP 68 |
| Entry thread | Pg 21 |
| Clamping range without insert min. | 6.8 mm |
| Clamping range without insert max. | 9.0 mm |
| Number of cables | 3 |
| Wrench size | 34 mm |
| Dimension H | 33 mm |
| Thread length L | 13 mm |
| Dispatch | 25 |

Additional versions and colours are available upon request: e.g. dark grey RAL 7001, black RAL 9005, larger entry threads