

## Synthetic Syntec® cable glands with lamellar technology and anti-kink nozzle



### Entry thread Pg

#### Type approval: SYNTEC mit Knickschutz

- Light grey RAL 7035
- One-piece sealing ring

<b>Order number:</b>	<b>1576.16.11</b>
E-No:	121780409
EAN:	7611614078861
Material	Polyamide PA 6
Properties	halogen-free, black UV resistant (tested according to EN ISO 4892-2)
Sealing ring	CR (neoprene)
Operation temperature	-30°C / +100°C
Protection class	IP 68
NEMA Type rating	4X
Entry thread	Pg 16
Clamping range min.	5.0 mm
Clamping range max.	11.0 mm
Wrench size	27 mm
Dimension H	102 mm
Thread length L	10 mm
UL - clamping range	6.5-11.0 mm
Dispatch	50