



Klemsan®

551022 KKC 1008

100x80 Slotted wiring duct,Grey

| | | |
|------------------------------------|---------------------|----------------|
| General Product Information | Insulating material | PVC - UL 94 V0 |
| Operating Temperature | Minimum Temperature | -15°C |
| | Maximum Temperature | +60°C |
| Dimensions | A | 100 mm |
| | B | 80 mm |
| | C | 16 mm |
| | D | 4 mm |
| | E | 6 mm |
| | F | 2,1 mm |
| | G | 4,5 mm |
| | H | 6,5 mm |
| | I | 25 mm |
| | Length | U |
| Product Information | Packing Unit | 8x2 |
| | Working range | |



UL Sertifikası - UL Certificate

Alçak Gerilim direktiflerine uygunluk belgesi - VDE Certificate

Rusya Yangın Sertifikası - Rusya Yangın Sertifikası

Ukrayna Uygunluk Sertifikası - Ukrayna Uygunluk Sertifikası

Avrupa standartlarına uygunluk belgesi - CE Certificate

Türk Standartlarına Uygunluk Belgesi - Wiring Duct TSE certificate

| | Order Info | Dimensions |
|---|-------------------|--------------------------------------|
| ■ | 551022 100x80 | 100x80 Slotted wiring duct,Grey |
| ■ | 551022WS | 100x80 Wide slotted wiring duct,Grey |
