

## EMC lock nuts nickel-plated brass with cutter teeth



## Entry thread metric

<b>Order number:</b>	<b>8020.85</b>
E-No:	126383502
EAN:	7611614117447
Material	Nickel-plated brass
Operation temperature	-60°C / +200°C
Execution	EMC lock nut with cutting teeth for optimised shield contact
Entry thread	M20x1.5
Wrench size	24 mm
Material thickness	4.0
Packaging inner/dispatch	25/2000

1 = Metric coarse-pitch thread