

Synthetic locking plugs



Synthetic locking plugs

- Light grey RAL 7035
- without O-Ring

Order number:	8811
E-No:	126222012
EAN:	7611614013534
Material	Shock-resistant polystyrene
Operation temperature	-20°C / +80°C
Protection class	IP 54
Entry thread	Pg 11
Diameter	22 mm
Dimension H	3.5 mm
Thread length L	6.5 mm
Dispatch	100