

## Synthetic locking plugs



### Synthetic locking plugs

- Light grey RAL 7035
- without O-Ring

<b>Order number:</b>	<b>8816</b>
E-No:	126222014
EAN:	7611614013558
Material	Shock-resistant polystyrene
Operation temperature	-20°C / +80°C
Protection class	IP 54
Entry thread	Pg 16
Diameter	27 mm
Dimension H	3.5 mm
Thread length L	6.5 mm
Dispatch	100