

## Synthetic locking plugs



### Synthetic locking plugs

- Light grey RAL 7035
- without O-Ring

<b>Order number:</b>	<b>8821</b>
E-No:	126222015
EAN:	7611614013565
Material	Shock-resistant polystyrene
Operation temperature	-20°C / +80°C
Protection class	IP 54
Entry thread	Pg 21
Diameter	33 mm
Dimension H	4.0 mm
Thread length L	8.0 mm
Dispatch	100