



Klemsan®

420120 PSK 1/12

General Product Information	Insulating material	—
	Inflammability class acc. to UL 94	—
	Packing Unit	—
	Weight (g)	—
TSE / CE Technical Data	Nominal Voltage	400 V ~
	Nominal Current	24 A
	Cross Section	2.5 mm ²
	Norm	EN 60998-2-1
VDE Technical Data	Nominal Voltage	— V ~
	Nominal Current	— A
	Cross Section	2.5 mm ²
	VDE Norm	IEC 60998-1/IEC 60998-2-1
UL / CSA Technical Data	Nominal Voltage	— V ~
	Nominal Current	— A
	Cross Section	2.5
Connection Data	Minimum solid strand cross section	— mm ²
	Maximum solid Strand cross section	— mm ²
	Minimum fine Strand cross section	— mm ²
	Maximum fine strand cross section	— mm ²
	AWG Conductor Range	—
	Connection Type	screw/vidal
	Insulation Stripping length	5 mm
	Tightening torque	0.4/0.6 Nm

Avrupa standartlarına uygunluk belgesi - CE Certificate

Türk Standartlarına Uygunluk Belgesi - TSE Certificate

LAPEM - RETIE Sertifikası - LAPEM - Retie Certificate

Order Info

420120

© 2022 Klemsan A.Ş.
www.klemsan.com