



Klemsan®

431002 SK 1

SK 1

General Product Information	Insulating material	PA
	Inflammability class acc. to UL 94	V2
	Packing Unit	—
	Weight (g)	—
	Continuous Operating Temp.	(min.-max.)
	DIN-EN 45545Z	
VDE Technical Data	Nominal Voltage	450 V ~
	Nominal Current	32 A
	Cross Section	2.5 mm ²
	VDE Norm	IEC 60998-1/IEC 60998-2
UL / CSA Technical Data	Nominal Voltage	300 V ~
	Nominal Current	32 A
	Cross Section	AWG/22-10
Connection Data	Minimum solid strand cross section	0.75 mm ²
	Maximum solid Strand cross section	4 mm ²
	Minimum fine Strand cross section	0.5 mm ²
	Maximum fine strand cross section	2.5 mm ²
	AWG Conductor Range	22-12
	Connection Type	screw/vidalr
	Insulation Stripping length	7 mm
	Tightening torque	0.4 Nm
SK Dimensions	L	95
	W	16

Declaration of Conformity - Declaration of Conformity Certificate

LAPEM - RETIE Sertifikası - LAPEM - Retie Certificate

Ukrayna Uygunluk Sertifikası - Ukrayna Uygunluk Sertifikası

Order Info

□	431002	SK 1
■	430002	SK 1
