



# Klemsan®

## 431022 SK 3

SK 3

<b>General Product Information</b>	Insulating material	PA
	Inflammability class acc. to UL 94	V2
	Packing Unit	—
	Weight (g)	—
	Continuous Operating Temp.	(min.-max.)
	DIN-EN 45545Z	
<b>VDE Technical Data</b>	Nominal Voltage	450 V ~
	Nominal Current	57 A
	Cross Section	6 mm <sup>2</sup>
	VDE Norm	IEC 60998-1/IEC 60998-2
<b>UL / CSA Technical Data</b>	Nominal Voltage	300 V ~
	Nominal Current	50 A
	Cross Section	AWG/14-18
<b>Connection Data</b>	Minimum solid strand cross section	1.5 mm <sup>2</sup>
	Maximum solid Strand cross section	6 mm <sup>2</sup>
	Minimum fine Strand cross section	1.5 mm <sup>2</sup>
	Maximum fine strand cross section	6 mm <sup>2</sup>
	AWG Conductor Range	14-82
	Connection Type	screw/vidalr
	Insulation Stripping length	10 mm
	Tightening torque	0.8 Nm
<b>SK Dimensions</b>	L	135
	W	22.5

Declaration of Conformity - Declaration of Conformity Certificate

---

LAPEM - RETIE Sertifikası - LAPEM - Retie Certificate

---

Ukrayna Uygunluk Sertifikası - Ukrayna Uygunluk Sertifikası

**Order Info**

■	430022	SK 3
┌	431022	SK 3