



Part Number: 37106

Hook-Up/Lead Wire UL AWM Style 3340 & 3374, (1) 6 AWG (84x25) TC, EPDM, 600V, 150°C

Product Description

One 6 AWG stranded (84x25) tinned copper conductor, EPDM insulation.

Technical Specifications

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	No. of Conductors
6	84x25	TC - Tinned Copper	1

Conductor Count:	1
Conductor Size:	6 AWG

Insulation

Material	Nominal Diameter	Nominal Wall Thickness	Min. Average Wall Thickness
EPDM - Ethylene Propylene Diene Monomer Rubber	0.383 in	0.088 in	0.08 in
EPDM - Ethylene Propylene Diene Monomer Rubber			

Outer Jacket Material

Material	Nominal Diameter
No Jacket	0.383 in

Electrical Characteristics

Conductor DCR

Nominal Conductor DCR
0.38 Ohm/1000ft

Shielding:	Unshielded
------------	------------

Current

Element	Max. Recommended Current [A]
Single conductor in free air @ 30C ambient	Single conductor in free air @ 30C ambient 155 amps

Voltage

UL Description	UL Voltage Rating
UL AWM 3340	600V RMS
UL AWM 3374	600 VRMS

Temperature Range

UL Temp Rating:	125°C Flexing, 150°C Stationary
Operating Temp Range:	-55°C To +150°C

Mechanical Characteristics

Bulk Cable Weight:	132 lbs/1000ft
--------------------	----------------

Standards

UL AWM Style:	UL Style 3340, UL Style 3374
CSA Rating:	600 V, 125°C

CSA Type:	CL1254
Military Specification:	N/A

Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/96/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU:	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU RoHS Compliance Date (yyyy-mm-dd):	2004-01-01
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

Flammability, LSOH, Toxicity Testing

UL Voltage Rating:	600 V RMS
--------------------	-----------

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Part Number

Variants

Item #	Color	Footnote
37106 010100	BLACK	
37106 010250	BLACK	F
37106 0102500	BLACK	C
37106 010500	BLACK	C F

Footnote:	F - MAY CONTAIN MORE THAN 1 PIECE. MINIMUM LENGTH OF ANY ONE PIECE IS 50'.
Footnote:	C - CRATE REEL PUT-UP.

© 2018 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.