LifeCycle Assurance



Digi AnywhereUSB Plus

Connect USB peripheral devices anywhere on a Local Area Network (LAN) via Ethernet without a locally-attached host computer

IoT business automation requires communication with various IT assets and peripherals located across an enterprise.

Digi AnywhereUSB Plus remote USB hubs give users the simplest and most direct connection options for existing equipment with a variety of USB 3.1 Gen 1 port options.

All models have Gigabit Ethernet support. 8- and 24-port models support 10 GB Ethernet with the option to use SFP+ connectors for fiber network connectivity. The 24-port models support dual Ethernet or dual SFP+ and optional Ethernet bonding for higher speeds and/or failover redundancy.

Digi AnywhereUSB 24 Plus is rack mountable with 24 USB 3.1 Gen 1 ports, while AnywhereUSB 8 Plus is desktop or rack mountable (with included rack ears) and AnywhereUSB 2 Plus is desktop or panel mountable with eight or two ports, respectively, and support for Gigabit Ethernet.

Digi AnywhereUSB Plus can be coupled with SOC 2® Type 2-compliant **Digi Remote Manager**, a cloud-based device configuration and security management platform, or **Digi On-Prem Manager** (local), to help users reduce downtime. An intuitive user experience makes installation smooth and easy with quick setup and configuration to monitor and maintain larger installations of remote Digi and third-party devices.

For enterprise and industrial customers who need remote or local USB ports and the higher speeds of USB 3.1 Gen 1 and Gigabit/10 Gigabit Ethernet, Digi AnywhereUSB Plus products give you an industry-leading connectivity solution.

Related Digi devices and software



Digi ConnectPort TS



Digi Connect IT 16/48



Accessories




Digi Remote Manager

Key features, benefits and applications

- Network-attached USB hubs easily connect USB peripheral devices to a PC from remote or virtual hosts
- Ideal for connecting USB devices over the network in virtualized environments such as VMware®
- AnywhereUSB 24 Plus is rack mountable with two power supplies and Ethernet connections for failover redundancy
- Access and monitor USB and serial devices over TCP/IP connection
- Supports multi-host connectivity for each USB port or group independently
- Built-in **Digi TrustFence** for device security, secure encrypted connections, ongoing monitoring and support
- Device management via **Digi Remote Manager** or air-gapped management via **Digi On-Prem Manager**
- 1-year **LifeCycle Assurance** with 24x7 Expert Support and Digi Remote Manager Premier included

Application example



© Digi International Inc. All rights reserved. **www.digi.com**

Digi LifeCycle Assurance

Digi LifeCycle Assurance provides an enhanced level of service and support on new deployments of Digi AnywhereUSB® Plus, Digi Connect® EZ, and Digi Connect® IT 16/48 to provide security, reliability and speed, as well as ongoing device management.

Management
Digi Remote Manager®, our network orchestration platform, provides complete visibility and control, with configuration, remote monitoring, automation, security and OTA software update capabilities.

Device
High-performance, purpose-built Digi devices, with integrated software, designed to meet the requirements of a wide range of enterprise, industrial, medical and transportation use cases.

Technical Support
The support plan provides 24 x 7 x 365 tier 1 support with four-hour SLA for device and network troubleshooting to ensure your team can resolve issues quickly.

Warranty
Enjoy peace of mind with Digi's best-in-class warranty, covering your device for 5 years. Our technology transition support ensures that you can maximize your technology investment and mitigate risks effectively.

Digi Remote Manager and Digi On-Prem Manager



Digi Remote Manager (DRM) and **Digi On-Prem Manager** provide scalable, secure solutions for managing distributed IoT networks — whether in the cloud or on-premises.

SOC 2® Type 2-compliant DRM offers centralized, cloud-based control to deploy, monitor, and troubleshoot thousands of devices from any device — desktop, tablet, or phone — with built-in software-defined security.

Digi On-Prem Manager delivers similar capabilities within private, air-gapped, or regulatory-sensitive environments, keeping all data and management local.

Together, they offer flexible options to manage mission-critical networks — your way.

Learn more at digi.com/digi-remote-manager.

Digi Remote Manager and Digi On-Prem Manager

Flexible, secure IoT network management — in the cloud or on-premises

Core capabilities

- Activate, monitor and troubleshoot your mission-critical devices through a single portal
- Automate firmware updates, file management and configuration tasks across single or multiple devices
- Monitor device health, connectivity and performance across any deployment size
- Create detailed reports and real-time alerts for key metrics (signal quality, latency, data usage, etc.)
- Access edge devices via out-of-band console terminal
- Integrate device data into third-party systems via open APIs

Digi Remote Manager — cloud benefits

- Commercial-grade cloud server environment that 99.9% or greater uptime
- Compliant with SOC 1®, SOC 2® and SOC 3® standards
- Member of the Center for Internet Security® (CIS)
- Supports ISO27002, HIPAA, NIST and other frameworks
- Earned Skyhigh's CloudTrust™ Enterprise-Ready rating

Digi On-Prem Manager — local control

- All the essential DRM features, hosted within your private infrastructure
- Ideal for air-gapped, high-security, or regulatory-sensitive environments
- No data leaves your network — full control and compliance on-premises

Digi TrustFence



Designed for mission-critical applications, **Digi TrustFence** enables users to easily integrate device security, device identity, and data privacy capabilities into product design. Together with SOC 2 Type 2-compliant Digi Remote Manager, Digi TrustFence delivers unified, auditable security and compliance from device to cloud.

Learn more at digi.com/trustfence.


Built-In Security. Delivered.

- Unique password for each hub
- Configurable network service port numbers
- Secure access and authentication to the web UI and CLI
- One password, one permission level
- Selectively enable and disable network services such as mDNS, HTTP/HTTPS, and SSH
- Encrypted access to AnywhereUSB Plus traffic: Access to the USB-over-IP traffic is encrypted and authenticated by default and cannot be disabled
- Protected by the Digi TrustFence framework
- Manage Digi AnywhereUSB Plus remotely and securely with Digi Remote Manager, a comprehensive IoT device management application


© Digi International Inc. All rights reserved. **www.digi.com**

Product Images


Digi AnywhereUSB 2 Plus — front




Digi AnywhereUSB 2 Plus — back




Digi AnywhereUSB 8 Plus — front




Digi AnywhereUSB 8 Plus — back



Digi AnywhereUSB 24 Plus — front



Digi AnywhereUSB 24 Plus — back



© Digi International Inc. All rights reserved. **www.digi.com**

Specifications	Digi AnywhereUSB 2 Plus	Digi AnywhereUSB 8 Plus	Digi AnywhereUSB 24 Plus
CELLULAR			
MODULE SUPPORT	NA	(1) Digi CORE modem compliant socket	
SOFTWARE AND MANAGEMENT			
REMOTE MANAGEMENT	**Digi Remote Manager** (cloud based) or **Digi On-Prem Manager** (local)		
LOCAL MANAGEMENT	**Digi On-Prem Manager** (local), WebUI (HTTP/HTTPS); CLI (Console, SSH)		
OPERATING SYSTEMS	Windows®: Windows 7, 8.1, 10, 11; Windows Server® 2012-R2, 2016, 2019, 2022, 2025; Linux®: Ubuntu® (LTS versions tested 18.04, 20.04, 22.04, 24.04), Debian® (LTS versions tested 10.13, 11.9, 12.5) and Red Hat®/AlmaLinux/Rocky (LTS versions tested 8.10 and 9.4)		
PROTOCOLS	Supports multi-host connectivity for each USB port or group independently		
MEMORY	512 MB RAM, 4 GB flash (eMMC)	2 GB RAM, 4 GB flash (eMMC)	
NETWORK			
ETHERNET	(1) RJ-45; 10 M/100 M/1 G	(1) RJ-45; 10 M/100 M/1 G/10 G	(2) RJ-45; 10 M/100 M/1 G/10 G
SFP+	NA	(1) SFP+ socket	(2) SFP+ sockets
CONNECTORS			
CONSOLE	NA	(1) DB09M; RS-232 DTE	
USB	(2) USB 3.1 Gen 1 Type A	(8) USB 3.1 Gen 1 Type A	(24) USB 3.1 Gen 1 Type A
USB PORT POWER	1.8 A per port (simultaneous)	1 A per port (simultaneous)	
PHYSICAL			
DIMENSIONS (L X W X H)	118 mm x 74 mm x 30 mm (4.6 in x 2.9 in x 1.2 in)	260mm x 160 mm x 44.45 mm (10 in x 6 in x 1.75 in)	450.85 mm x 255 mm x 44.45 mm (17.75 in x 10 in x 1.75 in)
WEIGHT	0.38 kg (0.84 lb)	1.58 kg (3.48 lb)	4.7 kg (10.36 lb)
STATUS LEDS	Ethernet, 2x USB, power	Ethernet, SFP+, 8x USB, power, fan, user, 2x WWAN (if CORE module is inserted)	2x Ethernet, 2x SFP+, 24 USB, 2x PSU, 2x fan, user, 2x WWAN (if CORE module is inserted)
POWER REQUIREMENTS			
POWER INPUT	5 V, 5 A max	12 VDC, 12 A max	Dual 100-240 V, 3 A max (dual supplies for redundancy)
POWER CONSUMPTION	25 watts max	98.5 watts max	157.7 watts max
ENVIRONMENTAL			
OPERATING TEMPERATURE	0 °C to 40 °C (32 °F to 104 °F)	0 °C to 55 °C (32 °F to 131 °F)	
RELATIVE HUMIDITY	5% to 95% (non-condensing)		
APPROVALS*			
SAFETY*	UL 62368/60950, EN 62368, IEC 62368, CSA 22.2 62368 -1		
EMISSIONS/IMMUNITY*	CE, FCC Part 15 Class B, AS/NZS CISPR 22, EN 55024, EN 55032		
WARRANTY			
PRODUCT WARRANTY	5-year		
LIFECYCLE ASSURANCE	**1-year Digi LifeCycle Assurance** includes: 24×7 expert support and centralized device management via **Digi Remote Manager** (cloud) or **Digi On-Prem Manager** (local)		

*Visit **digi.com/resources/certifications** for latest updates.

Enterprise Software	Description
PROTOCOL SUPPORT	HTTPS, FTP, SFTP, TLS 1.2, SMTP, SSH and CLI for web management; **Digi Remote Manager** (cloud) or **Digi On-Prem Manager** (local)
SECURITY/VPN	TLS 1.2, SSH, HTTPS
ROUTING/FAILOVER	Ethernet bonding (AnywhereUSB 24 Plus only)
OTHER PROTOCOLS	DHCP

© Digi International Inc. All rights reserved. **www.digi.com**

Part Numbers	Digi AnywhereUSB Plus
Digi AnywhereUSB 2 Plus	
AW02-G300-GLB	Digi AnywhereUSB 2 Plus — dual USB 3.1 Gen 1 ports, single 10 M/100 M/1 G Ethernet, 5 VDC, includes power supply (76000965)
AW02-G300	Digi AnywhereUSB 2 Plus — dual USB 3.1 Gen 1 ports, single 10 M/100 M/1 G Ethernet, 5 VDC (power supply sold separately)*
Digi AnywhereUSB 8 Plus	
AW08-G300	Digi AnywhereUSB 8 Plus — 8-port USB over IP remote USB 3.1 hub with 10 M/100 M/1 G/10 G Ethernet, 12 VDC, SFP+ module support and optional cellular Digi CORE module, includes power supply, rack mount extension kit with attachable 19" rack ears
Digi AnywhereUSB 24 Plus	
AW24-G300	Digi AnywhereUSB 24 Plus — 24-port USB over IP remote USB 3.1 hub with dual 10 M/100 M/1 G/10 G Ethernet, dual 100-240 VAC power, dual SFP+ modules support and optional cellular Digi CORE module, includes rack mount extension kit

Part Numbers	Digi AnywhereUSB Plus Accessories
Digi AnywhereUSB 2 Plus Power Supply	
76000965	AC power supply — extended temperature, universal plugs (US, EU, UK, AU) to 5 VDC - 2.5 mm locking barrel plug (6 A max)*
Digi AnywhereUSB 2 Plus DIN Mounting Bracket	
76000682	DIN rail mounting kit for AnywhereUSB 2 Plus
Digi AnywhereUSB 24 Plus CORE LTE Plug-In Modem	
1002-CMG4-GLB	Digi CORE plug-in LTE modem; Global LTE Cat 4, 3G/2G fallback

*Recommended power supply for AnywhereUSB 2 Plus, provides full USB charging capability of 1.8 A per port.

Part Numbers	Digi LifeCycle Assurance
DIGI-IM-LCA-1YR-EXT	Digi LifeCycle Assurance — 1-year extension
DIGI-IM-LCA-2YR-EXT	Digi LifeCycle Assurance — 2-year extension
DIGI-IM-LCA-3YR-EXT	Digi LifeCycle Assurance — 3-year extension
DIGI-IM-LCA-4YR-EXT	Digi LifeCycle Assurance — 4-year extension
DIGI-IM-LCA-RENEWAL	Digi LifeCycle Assurance renewal

Part Numbers	Digi LifeCycle Assurance with On-Prem Manager
Digi LlfeCycle Assurance On-Prem Manager Server	
DIGI-IM-LCAP-SERVER-1YR	Digi LifeCycle Assurance On-Prem Manager Server License — 1-year subscription
DIGI-IM-LCAP-SERVER-2YR	Digi LifeCycle Assurance On-Prem Manager Server License — 2-year subscription
DIGI-IM-LCAP-SERVER-3YR	Digi LifeCycle Assurance On-Prem Manager Server License — 3-year subscription
DIGI-IM-LCAP-SERVER-4YR	Digi LifeCycle Assurance On-Prem Manager Server License — 4-year subscription
DIGI-IM-LCAP-SERVER-5YR	Digi LifeCycle Assurance On-Prem Manager Server License — 5-year subscription
Digi On-Prem Manager Per-Device Licence	
DIGI-IM-LCAP-1YR-REN	Digi LifeCycle Assurance On-Prem Manager — renewal
DIGI-IM-LCAP-1YR-EXT	Digi LifeCycle Assurance On-Prem Manager — 1-year extension
DIGI-IM-LCAP-2YR-EXT	Digi LifeCycle Assurance On-Prem Manager — 2-year extension
DIGI-IM-LCAP-3YR-EXT	Digi LifeCycle Assurance On-Prem Manager — 3-year extension
DIGI-IM-LCAP-4YR-EXT	Digi LifeCycle Assurance On-Prem Manager — 4-year extension
DIGI-IM-LCAP-5YR-EXT	Digi LifeCycle Assurance On-Prem Manager — 5-year extension

© Digi International Inc. All rights reserved. **www.digi.com**

Part Numbers	Digi Remote Manager
DIGI-RM-IM-PRM-1YR	Digi Remote Manager Premier — 1-year subscription
DIGI-RM-IM-PRM-3YR	Digi Remote Manager Premier — 3-year subscription
DIGI-RM-IM-PRM-5YR	Digi Remote Manager Premier — 5-year subscription

Part Numbers	Expert Support
DG-EXPE-24	Digi 24×7 Support for end users

Part Numbers	Value-Added Services*
DANI — Digi Artificial Network Intelligence Value-Added Services and Subscriptions	
DIGI-RM-AI-STARTER-1YR	DANI Starter — per-user seat license, DRM AI assistant, pooled account credits, annual term
DIGI-RM-AI-PRO-1YR	DANI Pro — per-user seat license, DRM AI assistant, larger pooled credit allotment, annual term
Digi Containers Value-Added Services and Subscriptions	
DIGI-RM-PRM-CS	Digi Containers subscription — 1-year subscription

*DANI and Digi Containers are available as value-added services with Digi Remote Manager and compatible devices.

LifeCycle Assurance

Digi LifeCycle Assurance includes: 24×7 expert support and centralized device management via **Digi Remote Manager** (cloud) or **Digi On-Prem Manager** (local).

For more information, please visit digi.com.

For more information about Digi AnywhereUSB Plus, visit **digi.com/anywhereusb-plus**.

877-912-3444 | **952-912-3444**

© 2026 Digi International Inc. All rights reserved. All other trademarks are the property of their respective owners.

91004384
D2/726