





JKL PART NO.: 2910F-42



JKL PART NO.: 2910F-47

NOTES:

- TAB SIZE REFERENCE DIMENSIONS: .244" wide X .30" deep X .016 thick.
KEYSTONE P/N 4470 QUICK-FIT SOCKET MAY BE USED FOR CONTACT.
- LAMP SIZES FOR EACH HOLDER:
-42 HOLDER CAN HOLD LAMPS FROM 38mm TO 43mm LONG
-47 HOLDER CAN HOLD LAMPS FROM 40mm TO 44mm LONG
- MINIMUM CONTACT DIAMETER .30"
- LOCATION OF MOUNTING HOLE. HOLE DIA. : Ø3.5mm REF.
- BODY MATERIAL: DUPONT FR50
MAX. WITHSTAND TEMPERATURE 130C
MAX. INTERMITTENT TEMPERATURE 180C
MAX. WATTAGE: -42 10W
-47 18W

			METRIC  THIRD ANGLE PROJECTION		DIMENSIONS ARE IN MILLIMETERS TOLERANCE UNLESS OTHERWISE SPECIFIED 1 PL +/- REF. 2 PL +/- REF. ANGLE +/- 0		JKL COMPONENTS CORPORATION				
F	CHANGE NOTE 2 HOLDER SIZES	8/23/12	DRAWN BY L. WENGSTROM		APPV'D BY L. R. DATE 8/23/12		TITLE FESTOON HOLDER				
E	CHANGE NOTE 2	3/9/10									
D	ADDED NOTES	8/7/08									
C	CORR. MATERIAL DESCRIPTION	11/13/07									
B	ADD NOTES	8/18/06									
A	ADD PART NO. 2910F-47	6/30/06					SIZE	FSCM NO.	DRAWING NO.		
	RELEASED	6/12/06					A	55335	2910F		
REV. NO.	DESCRIPTION/ECO NUMBER	APPV'D DATE	- CAD DRAWING - MANUAL REVISIONS NOT PERMITTED			SCALE		RELEASED DATE	REVISION DATE	REV. NO.	SHEET
						NONE		6/12/06	8/23/12	F	1 OF 1