GE1MC7-P06LFD0-0000

ODU MEDI-SNAP®

Not available anymore - alternative: G4 in size 1

Basic information

Part number	GE1MC7-P06LFD0-0000
Category	Connector

Contact insert description

Number of contacts	6
Contact type	Sockets
Contact diameter	0.7 mm
Termination type	Solder cup
Termination diameter	0.65 mm

Technical information

Nominal current single contact	6 A

Mechanical and environmental data

Keying	Coding 60°
Mating cycles	5.000
Max. operating temperature	120 °C
Min. operating temperature	-50 °C
Weight	6 g

Material and surface treatments

Insulator material	PEEK
Contact material	Cu-alloy with gold finish

Further technical information and downloads

3D-File (STP File)