GE1MC7-P10LCC0-0000

ODU MEDI-SNAP®

Not available anymore - alternative: G4 in size 1

Basic information

Part number	GE1MC7-P10LCC0-0000
Category	Connector

Contact insert description

Number of contacts	10
Contact type	Sockets
Contact diameter	0.5 mm
Termination type	Solder cup
Termination diameter	0.45 mm

Technical information

Nominal current single contact	4 A

Mechanical and environmental data

Keying	Coding 60°
Mating cycles	5.000
Max. operating temperature	120 °C
Min. operating temperature	-50 °C
Weight	9.999 g

Material and surface treatments

Insulator material	PEEK
Contact material	Cu-alloy with gold finish

Further technical information and downloads

3D-File (STP File)