



Not available anymore - alternative: G4 in size 1

Basic information

Part number	GE1MC8-P08QF00-0000
Category	Connector

Mechanical and environmental data

Max. operating temperature	120 °C
Min. operating temperature	50 °C

Further technical information and downloads

3D-File (STP File)
