

**Liquidtight Flexible Cord & Cable Fittings****T&B Catalog Number:**

035-72775-26

**UPC Number:**

78621086851

**Status:**

Active

**Description:**

1-1/2 Inch straight die cast zinc liquidtight strain relief cord connector, cord range-1.000-1.187.

**Features**

Throat inner diameter is nylon coated for ease of wire pull

Extended range with superior strain relief

**Application**

Provide means for passing a cord cable, armored or unarmored, into an enclosure, through a bulkhead or into a rigid conduit

**General**

Material Die Cast Zinc

**Dimension Information**

Hub Size (inches) 1 1/2

Cord Range (inches) 1.000-1.187

**Packaging**

T&B Inner Pack 5

Package in Units 10

T&B Sold in UOM Each

T&B Weight Per UOM 72 lbs. per 100

**Certifications**

RoHS Compliance Yes

**Certifications**

File Nbr:

E 13938

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
www.tnb.com

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email:techsupport@tnb.com