



RAST

TE Internal #: 1-1241965-4

4 Position, Plug, Housing, Insulation Displacement (IDC), Wire-to-Board, 5 mm [.197 in] Centerline, 1 Row, Wire & Cable, Power & Signal

[View on TE.com >](#)

Connectors > Rectangular Connectors > Standard Rectangular Connectors



Connector Product Type: **Housing**
Connector & Housing Type: **Plug**
Mating Retention Type: **Latch**
Connector System: **Wire-to-Board**
Number of Positions: **4**

Features

Product Type Features

Connector Product Type	Housing
Connector & Housing Type	Plug
Connector System	Wire-to-Board
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	4
Number of Rows	1

Body Features

Primary Product Color	Natural
-----------------------	---------

Termination Features

Termination Method to Wire & Cable	Insulation Displacement (IDC)
------------------------------------	-------------------------------

Mechanical Attachment

--	--



Mating Retention Type	Latch
Mating Retention	With
Connector Mounting Type	Cable Mount (Free-Hanging)

Housing Features

Centerline (Pitch)	5 mm [.197 in]
--------------------	----------------

Usage Conditions

Operating Temperature Range	-40 – 105 °C [-40 – 221 °F]
-----------------------------	-----------------------------

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not reviewed for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts



TE Part # 1241965-6
STD-TIMER GEH 6P




TE Part # 2-1241965-7
7P ST-TIMER GEH




TE Part # 1-1241965-6
6POS STD TIMER HOUSING W.EXT. LOCK



TE Part # 2345754-1
STD TIMER PLUG HSG 2P W/EXT. LOCKING



TE Part # 1241965-8
8POS STD TIMER HSG WITH EXT. LOCKING




TE Part # 8-1241965-2
STD TIMER PLUG HSG 2P W/EXT. LOCKING




TE Part # 1241965-4
STANDARD TIMER HSG. WITH EXT. LOCK.



TE Part # 1241965-3
3P ST-TIMER GEH



TE Part # 4-1241965-2
STD TIMER HOUSING



TE Part # 1241965-2
STD TIMER HOUSING 2POS


Customers Also Bought



TE Part #917691-1
2.5 SIGNAL D/LOCK PLUG HSG 7P



TE Part #917703-1
2.5 SIGNAL D/LOCK D.L.P 7P



TE Part #2-1241965-4
STD TIMER PLUG HSG 4P W/EXT. LOCKING




TE Part #6-1241965-5
STD TIMER PLUG HSG 5P W/EXT. LOCKING



TE Part #1747995-2
GHC EYELET 6.2 3POS PLUG HOUSING RED



TE Part #4-2232890-0
10P MONOPLUG 2.5 SELECTIVELY LOADED



TE Part #1-2232892-4
4P MONOPLUG 2.5



TE Part #2324841-1
PDL 3.96MM CAP HOUSING 9 POS, F /H



Documents

Product Drawings

STD TIMER PLUG HSG 4P W/EXT.LOCKING

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1-1241965-4_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1-1241965-4_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1-1241965-4_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

RAST Connector System Catalog

English

Product Specifications

Product Specification

German

Agency Approvals

VDE Certificate

English