



Switches > Rocker Switches



Switch Type: **High Power Rocker Switch**

Product Mount Type: **Panel Mount**

Indicator/Imprint Legend: **O I**

Panel Cutout Size: **21.2 x 37 mm [1.002 x 1.086 in]**

Switch Contact Plating Material: **Silver**

Features

Product Type Features

Switch Type	High Power Rocker Switch
Actuator Type	Top
Actuator Style	Rocker
Switch Connection Type	Quick Connect Terminal

Configuration Features

Indicator/Imprint Legend	O I
Panel Cutout Size	21.2 x 37 mm[1.002 x 1.086 in]
Configuration (Pole-Throw)	Double Pole - Single Throw
Operating Function	On Off

Electrical Characteristics

Power Rating	.33 hp
Contact Current Rating	16 A
Operating Voltage Range	125 VAC

Body Features

--	--

Product Orientation	Vertical
Actuator Color	Black

Contact Features

Terminal Tab Width	6.35 mm[.25 in]
Switch Contact Plating Material	Silver

Mechanical Attachment

Product Mount Type	Panel Mount
--------------------	-------------

Housing Features

Process Sealed	No
----------------	----

Industry Standards

Compatible With Agency/Standards Products	VDE
Compatible With Approved Standards Products	UL E46765

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides

PRDDA1-16F-BB0HW

High Power Rocker Switch, Panel Mount, 21.2 x 37 mm [1.002 x 1.086 in] Panel Cutout,
Silver Contact Plating



on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1571103-3
PRDDA1-16F-BB0CW,POWER
ROCKER



TE Part # 1571113-6
PRDDD3-16F-BB0GW=POWER
ROCKER



TE Part # 1571113-1
PRDDD1-16F-BB000,POWER ROCKER



TE Part # 1571103-1
PRDDA1-16F-BB000,POWER ROCKER



TE Part # 1571113-4
PRDDD3-16F-BB000=POWER ROCKER

Customers Also Bought



TE Part #DT04-2P
REC, 2P, GRY, N



TE Part #DT06-2S
PLG, 2P, GRY, N




TE Part #CAT-D48-ST273
DEUTSCH Connector Solid Contacts



TE Part #CAT-D487-W416
Wedgelocks: DEUTSCH DT



TE Part #114017-ZZ
SEALING PLUG, SIZE 12/16, WHT



TE Part #281934-2
SINGLE WIRE SEAL



TE Part #CAT-AM71-CH8172
AMP SUPERSEAL 1.5MM,
CONNECTOR HOUSING

Documents

- CAD Files
- 3D PDF
- 3D



Customer View Model

[ENG_CVM_CVM_1571103-5_F.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1571103-5_F.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1571103-5_F.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[1654742_HOUSEHOLD_APPLIANCES_RAST5](#)

English

[8-1773450-9_SWITCHES_CATALOG_SECTION_F_ROCKER/PADDLE_SWITCHES](#)

English