

LR1F121R

✓ ACTIVE

NEOHM | NEOHM LR

TE Internal #: 1622309-1

121 ohm, Thin Metal Film, General Purpose Resistor, 1 %, .6 W, ±50 ppm/°C, Axial-Leaded, Copper Termination, 6.8 x 2.5 mm, Ammo Packed, NEOHM LR

[View on TE.com >](#)



Passive Components > Resistors > Through-Hole Resistors



Resistor Type: **General Purpose Resistor**
Element Type: **Thin Metal Film**
Power Rating: **.6 W**
Resistance Class: **Up to 1kΩ**
Resistance Value: **121 Ω**

Features

Product Type Features

Resistor Type	General Purpose Resistor
Element Type	Thin Metal Film

Configuration Features

Number of Resistors	1
---------------------	---

Electrical Characteristics

Operating Voltage	250 V
Power Rating	.6 W
Resistance Class	Up to 1kΩ
Resistance Value	121 Ω
Passive Component Tolerance	1 %

Body Features

Lead Type	Axial-Leaded
-----------	--------------

Termination Features

Termination Area Base Material	Copper
Number of Terminations	2

Dimensions

Passive Component Dimensions	6.8 x 2.5 mm
------------------------------	--------------



Usage Conditions

Operating Temperature Range	-55 – 155 °C[-67 – 311 °F]
Temperature Coefficient	±50 ppm/°C

Packaging Features

Packaging Method	Ammo Packed
------------------	-------------

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

LR1F121R

121 ohm, Thin Metal Film, General Purpose Resistor, 1 %, .6 W, ±50 ppm/°C, Axial-Leaded, Copper Termination, 6.8 x 2.5 mm, Ammo Packed, NEOHM LR



TE Part # 1622598-1
LR1L 5% R10



TE Part # 1622742-1
LR2 1% 39K



TE Part # 1614978-1
LR0204 1% 10K



TE Part # 1622298-1
LR1 1% 10K



TE Part # 1622367-1
LR1 1% 1M0

Also in the Series | NEOHM LR



DIMM Sockets(5)



Through-Hole Resistors(490)


Customers Also Bought



TE Part #203323-E
MJIM IMV 1X1 S 88 * X R THRU * L1 M3D01



TE Part #1-338068-0
MICRO-MATCH FTE,10P



TE Part #3-641215-3
03P MTA100 HDR ASSY FL/ST 30AU



TE Part #1-770170-0
03P MINI-UMNL ASSY VO SNNI*



TE Part #1-1393219-0
PE014024



TE Part #1622345-1
LR1 1% 18K2



TE Part #1622462-1
LR1 1% 3K32



TE Part #2-1676481-2
CPF 0603 39R 0.1% 25PPM 1K RL

LR1F121R

121 ohm, Thin Metal Film, General Purpose Resistor, 1 %, .6 W, ±50 ppm/°C, Axial-Leaded, Copper Termination, 6.8 x 2.5 mm, Ammo Packed, NEOHM LR



Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1622309-1_BA.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1622309-1_BA.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1622309-1_BA.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

1309350_PASSIVE_COMPONENT

English

Metal Film Fixed Resistors - Type LR series

English