




Automotive Parts > Automotive Connector Accessories > Other Automotive Connector Accessories



Primary Product Material: **Stainless Steel**

Automotive Connector Accessory Type: **Pressure Spring Contact**

Operating Temperature Range: **-40 – 140 °C [-40 – 284 °F]**

Features

Product Type Features

Automotive Connector Accessory Type	Pressure Spring Contact
-------------------------------------	-------------------------

Body Features

Primary Product Material	Stainless Steel
--------------------------	-----------------

Usage Conditions

Operating Temperature Range	-40 – 140 °C[-40 – 284 °F]
-----------------------------	----------------------------

Packaging Features

Packaging Method	Box
Packaging Quantity	630

Other

Serviceable	No
-------------	----

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant





China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 7-2371496-7 CRIMP TOOLING KIT	 TE Part # 5-1991226-2 1 POS. RING TONGUE HOUSING ASSY. IPT 16-	 TE Part # 3-1991226-2 1 POS. RING TONGUE HOUSING ASSY. IPT 16-	 TE Part # 2141783-2 3POS,RING TONGUE,HSG,ASSY, SEALED
 TE Part # 9-2351900-1 APPLIC IPT-180-1/2/3P F 50MM2	 TE Part # 2371496-1 DIE SET IPT-180-1/2/3P F 25MM2	 TE Part # 2141784-2 2POS,RING TONGUE,HSG,ASSY, SEALED	 TE Part # 7-2234154-7 CRIMP TOOLING KIT






HV APPLICATOR
REPRESENTATION ONLY. DIE SET MAY VARY.

TE Part # 9-2351900-2
APPLIC IPT-180-1/2/3P F 50MM2




TE Part # 1-1991226-2
1 POS. RING TONGUE HOUSING
ASSY. IPT 16-




TE Part # 6-1991226-2
1 POS. RING TONGUE HOUSING
ASSY. IPT 16-




TE Part # 2-1991226-2
1 POS. RING TONGUE HOUSING
ASSY. IPT 16-



TE Part # 2234154-1
DIE SET2 IPT-180-1/2/3P F 35MM2




TE Part # 2351900-1
DIE SET2 IPT-180-1/2/3P F 50MM2



HV APPLICATOR
REPRESENTATION ONLY. DIE SET MAY VARY.

TE Part # 9-2371496-1
APPLIC IPT-180-1/2/3P F 25MM2



TE Part # 2351900-2
DIE SET2 IPT-180-1/2/3P F 50MM2



TE Part # 7-2351900-7
CRIMP TOOLING KIT



TE Part # 4-1991226-2
1 POS. RING TONGUE HOUSING
ASSY. IPT 16-



TE Part # 9-1991226-2
1 POS. RING TONGUE HOUSING
ASSY. IPT 16-

Also in the Series | IPT / APT



Automotive Connector Caps & Covers
(1)



Automotive Seals & Cavity Plugs(1)



Automotive Terminals(1)



Connector Seals & Cavity Plugs(1)








High Voltage Wire Processing
Equipment(15)



Other Automotive Connector
Accessories(2)

Customers Also Bought



 TE Part #2358669-4 SHIELDING SLEEVE	 TE Part #2141784-2 2POS, RING TONGUE, HSG, ASSY, SEALED	 TE Part #2177526-3 ANTI ROTATION SAFEGUARD-HV-1P, IPT, 35mmsq	 TE Part #2209387-2 BYD 6DT35 CABLE ASSY
 TE Part #2310540-4 HVA280 2P HEADER ASSY, KEY D	 TE Part #3-2315661-2 3POS. RING TONGUE HSG, ASSY S	 TE Part #2497871-1 PDU ASSY, PLUG HOUSING ASSEMBLY	 TE Part #2497881-1 PDU ASSY, AL BAR COVER SEAL
 TE Part #2497886-1 PDU ASSY, COPPER RING	 TE Part #2497892-1 PDU ASSY, TPA		

Documents

Product Drawings
CONTACT KIT, BODY AND SPRING,
English

CAD Files
3D PDF
3D
Customer View Model
ENG_CVM_CVM_2141809-3_B.2d_dxf.zip
English
Customer View Model
ENG_CVM_CVM_2141809-3_B.3d_igs.zip
English
Customer View Model
ENG_CVM_CVM_2141809-3_B.3d_stp.zip
English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications



Application Specification

English