




Application Tooling > Hand Crimping Tools



Tool Grade: Commercial Crimp Tooling

Die Sets Type: Removable/Interchangeable

Specification Type: TE Product Specification (114-)

TE Certification: Cannot be Certified

Tooling Type: SDE Crimp Die Set

Features

Other

Crimp Form-Wire Barrel Type	Open Barrel - F Crimp
Tool Grade	Commercial Crimp Tooling
Die Sets Type	Removable/Interchangeable
Specification Type	TE Product Specification (114-)
TE Certification	Cannot be Certified
Tooling Type	SDE Crimp Die Set

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Out of Scope
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250)



Candidate List Declared Against: JUNE 2025 (250)
Does not contain REACH SVHC

Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 929924-2
STD PW TIMER CONTACT (LP)

TE Part # 2379968-1
SDE F POWER TIMER 0.50-4.00 ASSY

TE Part # 2362810-1
SDE CRIMP HAND TOOL FRAME W /O DIES

Customers Also Bought

TE Part #HDC16-5-LA
DUST CAP, 5P, REC, GRY, LANYARD, HD10

TE Part #SRK-SC-080-25-601
SOC, SOLID, SIZE M8, 25mm2, AG

TE Part #776273-1
14POS,AMPSEAL,SOC HSG ASSY,SLD, COD 1

TE Part #2-964273-1
JPT A REC 2.8 Contact SWS Au COD 1





TE Part #1-967622-1

JUN-POW-TIM-GEH 12P



TE Part #1-1355122-2

SHIELD, 60POSN. RECEPTACLE HOU



TE Part #1-1718484-4

CARRIER FOR RECEPTACLE INSERTS



TE Part #2-1823449-1

22POS, MIXED,TAB HSG,ASSY



TE Part #2236721-1

ADAPTER, FOR TAB HOUSING, ASSY



TE Part #2362810-1

SDE CRIMP HAND TOOL FRAME W /O DIES

Documents

Datasheets & Catalog Pages

Bottoming Dies

English

Instruction Sheets

Instruction Sheet (U.S.)

English