

RP73D1J28R7BTG

✓ ACTIVE

Holsworthy | Holsworthy RP73


TE Internal #: 7-1879743-6

28.7 ohm, Thin Film, Precision Resistor, .1 %, 0603, .1 W, ±15 ppm/°C, Solder, 2 Terminations, .45 mm [.018 in] Height, Holsworthy RP73

[View on TE.com >](#)



Passive Components > Resistors > Surface Mount Resistors



Resistor Type: Precision Resistor

Element Type: Thin Film

Package Size Code: 0603

Power Rating: .1 W

Resistance Value: 28.7 Ω

Features

Product Type Features

Resistor Type	Precision Resistor
Element Type	Thin Film
Package Size Code	0603

Configuration Features

Number of Resistors	1
---------------------	---

Electrical Characteristics

Operating Voltage	75 V
Power Rating	.1 W
Resistance Value	28.7 Ω
Resistance Class	Up to 1kΩ
Passive Component Tolerance	.1 %

Termination Features

Surface Mount Resistor Termination Type	Solder
Number of Terminations	2

Dimensions

Product Height	.45 mm[.018 in]
Product Length	1.55 mm[.061 in]
Product Width	.8 mm[.031 in]



Usage Conditions

Temperature Coefficient	±15 ppm/°C
-------------------------	------------

Industry Standards

Moisture Sensitivity Level	1
----------------------------	---

Packaging Features

Packaging Method	Cut Tape Length
------------------	-----------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 260°C


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts

RP73D1J28R7BTG


28.7 ohm, Thin Film, Precision Resistor, .1 %, 0603, .1 W, ±15 ppm/°C, Solder, 2 Terminations, .45 mm [.018 in] Height, Holsworthy RP73




TE Part # 9-1879252-4
RP 2B 10R 0.1% 15PPM CUT LENGTH




TE Part # 2-1879279-6
RP 2A 75K 0.1% 15PPM 1K RL



TE Part # 5-1879743-7
RP 1J 18R2 0.1% 15PPM CUT LENGTH



TE Part # 2-1879747-4
RP 1J 110K 0.1% 15PPM CUT LENGTH



TE Part # 5-1879267-0
RP 2B 1M0 0.1% 15PPM 1K RL

Also in the Series | [Holsworthy RP73](#)




[Surface Mount Resistors\(4227\)](#)

Customers Also Bought



TE Part #6-104809-1
12 MTE HDR SRST LATCH W/HLDWN



TE Part #487952-5
005 1MM FPC BTM HORZ



TE Part #4-644759-2
12P MTA156 HDR ASSY STR LF




TE Part #2-1445097-5
MICRO MNL HDR ASSY S/ROW AU LF



TE Part #2057183-1
1x4 QSFP Kit Assy LP&HS, PCI



TE Part #8-2176363-8
RQ 0402 3K48 0.1% 10PPM 5K RL



TE Part #3-2176388-4
RQ 1206 22R1 0.1% 10PPM 5K RL



TE Part #1761688-9
IDC LOW PRO HDR 26P VERT LAT

RP73D1J28R7BTG

28.7 ohm, Thin Film, Precision Resistor, .1 %, 0603, .1 W, ±15 ppm/°C, Solder, 2 Terminations, .45 mm [.018 in] Height, Holsworthy RP73



Documents

Product Drawings

RP 1J 28R7 0.1% 15PPM CUT LENGTH

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_7-1879743-6_BA.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_7-1879743-6_BA.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_7-1879743-6_BA.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

1309350_PASSIVE_COMPONENT

English

RP73-0915

English

8-1773459-4_POWER_FILTERING_AND_RESISTIVE_SOLUTIONS_FOR_ELEVATORS_AND_ESCALATORS

English