

 [Live Product Chat](#)



✓ Active

 Add to Part List

 Always EU RoHS/ELV Compliant (Statement of Compliance)

- Receptacle
- HV-100
- Number of Positions = 11
- Number of Rows = Dual
- Standard Profile

[View all Features](#) | [Find Similar Products](#)

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)
- ▶ [Request Samples](#)

NEW!

Product Drawings: • HV 100 VERTICAL CONNECTOR (TIF, German) Catalog Pages/Data Sheets: • None Available Product Specifications: • None Available Application Specifications: • None Available Instruction Sheets: • None Available CAD Files: (CAD Format & Compression Information) • 2D Drawing (DXF, Version C1) • 3D Model (IGES, Version C1) • 3D Model (STEP, Version C1) List all Documents	Additional Information: • Product Line Information Related Products: • Tooling
---	--

Product Features (Please use the Product Drawing for all design activity)

- Product Type = Receptacle
- Connector Series = HV-100
- Number of Positions = 11
- Profile = Standard
- Mount Angle = Vertical
- Mounting Pattern (mm [in]) = 2.54 [.100]
- Sealed = No
- Holddown Feature = Without
- PCB Retention Feature = Yes
- Closed Entry = With
- Board Standoff = With

- Stackable = Yes

- Termination Method = Through Hole
- Termination (Solder) Post Length (mm [in]) = 3.10 [0.122]
- Solder Tail Contact Plating = Tin

- Number of Rows = Dual
- Connector Height (mm [in]) = 7.00 [0.276]
- Centerline, Matrix (mm [in]) = 2.54 [.100]
- PCB Retention Method = Retention Solder Tails
- Closed Bottom = With

- Contact Mating Area Plating Material = Gold (30)
- Contact Material = Phosphor Bronze

- Housing Entry Style = Top
- Housing Material = Polyester GV
- Housing Flammability Rating = UL 94V-0
- Housing Color = Green

- Government/Industry Qualification = No
- RoHS/ELV Compliance = RoHS compliant, ELV compliant
- Lead Free Solder Processes = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
- RoHS/ELV Compliance History = Always was RoHS compliant

- Packaging Quantity = 64

- Brand = AMP