



Part No: 122A13089X

Product Description

- DIN EN 60603-2 (DIN 41612)
- Type D
- Female Connector
- 32-pos.
- Solder Pin straight diameter 0,7mm

[Inquiry](#)

General Data

Technical Data

Material Data

Downloads

min. working temperature	-55° C
max. working temperature	+125° C
Quality class	Quality class 3
Mating cycles	50
IP rating	IP 20
Insertion force	40 N
Extraction force	40 N
Contact resistance standard	15 mOhm