


Image gallery

3D view



Part No: 13-001713

Product Description

- D-SUB Combination Dual Port
- 2W2C/2W2C
- Dual port socket upper / Socket bottom
- Metal bracket
- UNC 4-40

[Inquiry](#)

General Data

Technical Data

Material Data

Standards

Downloads

Dielectric with standing voltage power	1000 V
min. working temperature	-55° C
Working voltage power	250 V
Quality class	Quality class 3
Mating cycles	50
IP rating	IP 20
Insertion force	14 N
Extraction force	14 N
Power resistance standard	1 mOhm