

Image gallery

3D view



Part No: 131A10019X

Product Description

- Combination D-SUB contacts
- Plug
- Solder cup

[Inquiry](#)

General Data

Technical Data

Material Data

Standards

Downloads

Dielectric with standing voltage power	1000 V
min. working temperature	-55° C
Power contact cross section	AWG 16- 20
Working voltage power	250 V
Quality class	Quality class 3
Mating cycles	50
IP rating	IP 20
Current rating power	10 A
Insertion force	7 N
Extraction force	5 N
Power resistance standard	1 mOhm