

Image gallery

3D view



Part No: 15-000823

Product Description

- IP67 D-SUB Solid Body
- 15-pos.
- Plug
- Solder pin angled .590°

[Inquiry](#)

General Data

Technical Data

Material Data

Standards

Downloads

Dielectric with standing voltage signal	1000 V
Quality class	Quality class 3
Mating cycles	50
IP rating	IP67
Insertion force	50 N
Extraction force	50 N
Contact resistance standard	10 mOhm
min. working temperature	-25° C
max. working temperature	+105° C