



Part No: 15-000853

Product Description

- IP67 D-SUB Solid Body
- 9-pos.
- Socket
- Solder pin angled .590"

[Inquiry](#)

General Data

Technical Data

Material Data

Standards

Downloads

Dielectric with standing voltage signal	1000 V
Quality class	Quality class 3
Mating cycles	50
IP rating	IP67
Insertion force	30 N
Extraction force	30 N
Contact resistance standard	10 mOhm
min. working temperature	-25° C
max. working temperature	+105° C