



Part No: 15-005913

Product Description

- IP67 Combination D-SUB
- 45W2 [.....o.....]
- Female Connector

Inquiry

General Data	Technical Data	Material Data	Standards	Downloads
Dielectric with standing voltage signal		1000 V		
Dielectric with standing voltage power		1000 V		
min. working temperature		-25° C		
max. working temperature		+105° C		
Working voltage power		250 V		
Quality class		Quality class 3		
Mating cycles		50		
IP rating		IP67		
Current rating power		20 A		
Insertion force		160 N		
Extraction force		23 N		
Contact resistance standard		10 mOhm		
Power resistance standard		2,7 mOhm		