

Image gallery

3D view



Part No: 15-006541

Product Description

- IP67 D-SUB CONEC SlimCon
- 9-pos.
- Plug
- Solder pin angled 8,3 mm

[Inquiry](#)

General Data

Technical Data

Material Data

Standards

Downloads

Dielectric with standing voltage signal	1000 V
Quality class	Quality class 1
Mating cycles	500
IP rating	IP67
Insertion force	30 N
Extraction force	30 N
Contact resistance standard	10 mOhm
min. working temperature	-40° C
max. working temperature	+105° C