


Image gallery

3D view



Part No: 15-007503

Product Description

- IP67 Combination D-SUB
- 7W2 [○●●●●●○]
- Plug

[Inquiry](#)

General Data

Technical Data

Material Data

Standards

Downloads

Dielectric with standing voltage signal	1000 V
Dielectric with standing voltage power	1000 V
min. working temperature	-40° C
max. working temperature	+105° C
Working voltage power	250 V
Quality class	Quality class 3
Mating cycles	50
IP rating	IP67 in connected condition
Current rating power	20 A
Power resistance standard	1 mOhm