



Part No: 163A13829X

Product Description

- D-SUB Standard
- 9-pos.
- Plug
- Solder pin angled .370"
- Plastic bracket
- Quality class 3
- UNC 4-40

[Inquiry](#)

General Data	Technical Data	Material Data	Standards	Downloads
Dielectric with standing voltage signal	1000 V			
Quality class	Quality class 3			
Mating cycles	50			
IP rating	IP 20			
Insertion force	<30 N			
Extraction force	<30 N			
Contact resistance standard	10 mOhm			
min. working temperature	-55° C			
max. working temperature	+125° C			