



Part No: 163A17899X

Product Description

- D-SUB High Density
- 26-pos.
- Plug
- Solder pin angled
- Metal bracket
- Quality class 3
- M3

[Inquiry](#)

General Data

Technical Data

Material Data

Standards

Downloads

Dielectric with standing voltage signal	1000 V
Quality class	Quality class 3
Mating cycles	50
IP rating	IP 20
Insertion force	<84 N
Contact resistance standard	10 mOhm
min. working temperature	-55° C
max. working temperature	+125° C