



Part No: 164A13009X

Product Description

- D-SUB Standard
- 9-pos.
- Socket
- Solder pin angled .370"
- Threaded Insert
- Quality class 3
- M3

[Inquiry](#)

General Data

Technical Data

Material Data

Standards

Downloads

Dielectric with standing voltage signal	1000 V
Quality class	Quality class 3
Mating cycles	50
IP rating	IP 20
Insertion force	<30 N
Extraction force	<30 N
Contact resistance standard	10 mOhm
min. working temperature	-55° C
max. working temperature	+125° C