

## Image gallery

## 3D view



## Part No: 164A13099X

## Product Description

- D-SUB Standard
- 15-pos.
- Socket
- Solder pin angled .370"
- Plastic bracket
- Quality class 3
- UNC 4-40

[Inquiry](#)

## General Data

## Technical Data

## Material Data

## Standards

## Downloads

|                                         |                 |
|-----------------------------------------|-----------------|
| Dielectric with standing voltage signal | 1000 V          |
| Quality class                           | Quality class 3 |
| Mating cycles                           | 50              |
| IP rating                               | IP 20           |
| Insertion force                         | <50 N           |
| Extraction force                        | <50 N           |
| Contact resistance standard             | 10 mOhm         |
| min. working temperature                | -55° C          |
| max. working temperature                | +125° C         |